



RODENT SCREEN KITS

Frame	Enclosure	Catalog Number	Disc. Sym.	App. Wgt. (lbs.)
182T-184T*	Open	175872	C	1
213T-215T*	Open	175871	C	1
254T-256T	Open	175873	C	2
284T-286T	Open	175874	C	3
324T	Open	175894	C	5
326T	Open	175875	C	4

*Rolled steel frame only.

- △ Use this kit for 182-4T and S213T motors with catalog numbers 131454 and higher, or with a G prefix. Both open and enclosed motors in this series use the same kits as ventilation is in the frame of the motor.
- * For use with 213T-215T 3450 RPM motors only.
- ◆ For use with motors having "P" suffix on date code.
- ▼ For use with motors having catalog numbers 15XXXX, G15XXXX, or 17XXXX.
- ✱ Not for use with WATTS-AVER® motors.
- ① For use with motors having date codes earlier than May 2003.
- ② For use with motors having date codes May 2003 and later.
- ◇ For use with 1140 and 1750 RPM motors only.
- ③ WATTS-AVER® II design, having oversized frame body.

SHADED FRAME INDICATES CAST IRON CONSTRUCTION